



# PILA LED ceiling

## Benefits

- Energy-efficient
- Wide application range



CRI



15,000 h



Non-dimmable



10,000\*



Lamp type	Power (W)	CCT (K)	Light output (lm)	Housing color	Diameter Ø (mm)	Height (mm)	EAN1	12NC
PILA Ceiling RD 10W 4000K W 06	10	4000	1100	White	250	68	8727900967807	915005778323
PILA Ceiling RD 17W 4000K W 06	17	4000	1900	White	320	68	8727900967821	915005778923



# PILA LED downlights

## PILA Downlights

### DN020B

- Bright and even light
- Energy-efficient
- Reliable performance



CRI



20,000 h



Non-dimmable



10,000x



Beam angle

Product type	Power (W)	CCT (K)	Light output (lm)	Height fix (mm)	Diameter Ø (mm)	EAN1	12NC
PILA DN020B LED13/830 14W D150 RD EU	14	3000	1300	38	165	8727900967845	929002668382
PILA DN020B LED13/840 14W D150 RD EU	14	4000	1300	38	165	8727900967869	929002668482
PILA DN020B LED22/830 22.5W D200 RD EU	22.5	3000	2200	38	225	8727900967883	929002668682
PILA DN020B LED22/840 22.5W D200 RD EU	22.5	4000	2200	38	225	8727900967906	929002668782



# PILA LED wall-mounted

## PILA wall-mounted

### WL007C

- Available with motion sensor
- Supports energy saving
- Available in round
- For wall and ceiling mounted



CRI



35,000 h



Non-dimmable



220-240 Vac



Safety Class



IP54

Product type	Power (W)	CCT (K)	Light output (lm)	Power factor	Mains voltage	Connection	EAN1	12NC
PILA WL007C LED10S/840 PSU RND WH G2	12	4000	1000	> 0.9	50-60Hz	Screwterminal	8710163364421	911401774752
PILA WL007C LED13S/840 PSU RND MDU WH	15	4000	1300	> 0.9	50-60Hz	Screwterminal	8710163335117	911401735142
PILA WL007C LED16S/840 PSU RND WH G2	20	4000	1600	> 0.9	50-60Hz	Screwterminal	8710163364438	911401774762



# PILA LED batten

## PILA batten

### BN007C

- Applicable for wide range of applications
- Supports energy saving
- Reliable quality



CRI



20,000 h



220-240 Vac



Safety Class



IP20

Lamp type	Power (W)	CCT (K)	Light output (lm)	Power factor	Mains voltage	Connection	EAN1	12NC
PILA BN007C LED30S/840 L1200	30	4000	3000	> 0.9	50-60Hz	Flywire 0.15m	8710163335087	911401735152



# PILA LED floodlights

## PILA Floodlights

### BVPO08

- Robust luminaire
- Supports energy savings
- Reliable quality



CRI



35,000 h



220-240 Vac



Safety Class



IP65



Product type	Power (W)	CCT (K)	Light output (lm)	Power factor	Mains voltage	Connection	EAN1	12NC
PILA BVPO08 10W 3000K	10	3000	900	> 0.9	50-60Hz	Flying wire	87195145329499	911401810583
PILA BVPO08 10W 4000K	10	4000	950	> 0.9	50-60Hz	Flying wire	87195145329899	911401820583
PILA BVPO08 20W 3000K	20	3000	1800	> 0.9	50-60Hz	Flying wire	87195145329399	911401811583
PILA BVPO08 20W 4000K	20	4000	1900	> 0.9	50-60Hz	Flying wire	87195145329799	911401821583
PILA BVPO08 50W 3000K	50	3000	4500	> 0.9	50-60Hz	Flying wire	87195145329199	911401814583
PILA BVPO08 50W 4000K	50	4000	4750	> 0.9	50-60Hz	Flying wire	87195145329599	911401824583
PILA BVPO08 100W 4000K	100	4000	9500	> 0.9	50-60Hz	Flying wire	87195145329499	911401826583
PILA BVPO08 200W 4000K	200	4000	19000	> 0.9	50-60Hz	Flying wire	87195145329399	911401828583

Product type	Power (W)	CCT (K)	Light output (lm)	Power factor	Length (mm)	Connection	EAN1	12NC
PILA BVPO08 20W 4000K MDU	20	4000	1900	> 0.9	50-60Hz	Flying wire	87195145329199	911401874983
PILA BVPO08 50W 4000K MDU	50	4000	4750	> 0.9	50-60Hz	Flying wire	87195145329799	911401875583



# PILA LED highbay

## PILA highbay

### BY007P

- Energy-efficient
- Wide application range
- Cuts glare with special glass cover



30,000 h



Non-dimmable



Safety Class



IP65



IK06

#### Product type

	Power (W)	CCT (K)	Light output (lm)	EAN1	12NC
PILA BY007P G2 LED100S/840 PSU WB	100	4000	10000	8719514958630	911401877884
PILA BY007P G2 LED150S/840 PSU WB	150	4000	15000	8719514958647	911401877984
PILA BY007P G2 LED200S/840 PSU WB	200	4000	20000	8719514958654	911401878084



# PILA LED panel

## PILA panel

### RC007B

- Wide application range
- Supports energy saving
- Reliable quality



CRI



35,000 h



220-240 Vac



Non-dimmable



Safety Class



IP20

Product type	UGR 19	Power (W)	CCT (K)	Light output (lm)	EAN1	12NC
PILA RC007B LED40S/840 PSU I W60L60 NOC	No	40	4000	4000	871951495997299	911401879584
PILA RC007B LED40S/840 PSU I W60L60 OC	Yes	40	4000	4000	871951495998999	911401879684



# PILA LED waterproof

## PILA waterproof

### WT007C

- Robust luminaire
- Supports energy saving
- Available in three sizes



CRI



35,000 h



220-240 Vac



Safety Class



IP65



IK06

Product type	Power (W)	CCT (K)	Light output (lm)	Power factor	Mains voltage	Connection	EAN1	12NC
PILA WT007C LED17S/840 PSU L600	17	4000	1700	> 0.9	50-60Hz	Wire	8710163343112	911401809680
PILA WT007C LED34S/840 PSU L1200	34	4000	3400	> 0.9	50-60Hz	Wire	8710163335148	911401735772
PILA WT007C LED34S/865 PSU L1200	34	6500	3400	> 0.9	50-60Hz	Wire	8710163335148	911401735772
PILA WT007C LED54S/840 PSU L1500	54	4000	5400	> 0.9	50-60Hz	Wire	8710163335155	911401735782
PILA WT007C LED54S/865 PSU L1500	54	6500	5400	> 0.9	50-60Hz	Wire	8710163351131	911401851180





# PILA LED waterproof classic

## PILA waterproof classic

### WT008C

- Clip-free robust luminaire
- Supports energy saving
- Available in three sizes and also with Through wiring option



CRI



35,000 h



220-240 Vac



Safety Class



IP65



IK08

Product type	Power (W)	CCT (K)	Light output (lm)	Power factor	Mains voltage	Connection	EAN1	12NC
PILA WT008C 20S/840 PSU L600 Classic	18	4000	2000	> 0.9	50-60Hz	-	8719514964907	911401813685
PILA WT008C 20S/840 PSU L600 TW Classic	18	4000	2000	> 0.9	50-60Hz	-	8719514964938	911401813985
PILA WT008C 40S/840 PSU L1200 Classic	36	4000	4000	> 0.9	50-60Hz	-	8719514964914	911401813785
PILA WT008C 40S/840 PSU L1200 TW Classic	36	4000	4000	> 0.9	50-60Hz	-	8719514964945	911401814085
PILA WT008C 60S/840 PSU L1500 Classic	53	4000	6000	> 0.9	50-60Hz	-	8719514964921	911401813885
PILA WT008C 60S/840 PSU L1500 TW Classic	53	4000	6000	> 0.9	50-60Hz	-	8719514964952	911401814185



# PILA LED tubes

## Benefits

- Reliable quality
- Energy-efficient



CRI



20,000 h



Non-dimmable



50,000+



Frequency(Hz)

Lamp type	LED (W)	CCT (K)	Light output (lm)	Input current (mA)	Dimension w × h (mm)	EAN1	12NC
PILA LED Tube 600mm 8W 840 G13	8	4000	800	70	28 × 603	8727900971071	929003130902
PILA LED Tube 600mm 8W 865 G13	8	6500	800	70	28 × 603	8727900971095	929003131002
PILA LED Tube 1200mm 16W 840 G13	16	4000	1600	134	28 × 1212	8727900971118	929003131102
PILA LED Tube 1200mm 16W 865 G13	16	6500	1600	134	28 × 1212	8727900971132	929003131202
PILA LED Tube 1500mm 19.5W 840 G13	19.5	4000	2000	155	28 × 1513	8727900971156	929003131302
PILA LED Tube 1500mm 19.5W 865 G13	19.5	6500	2000	155	28 × 1513	8727900971170	929003131402



# PILA LED lusters

## Benefits

- Up to 90% energy savings compared with halogen lamps
- Low maintenance costs
- Easy choice and installation
- Reliable quality



CRI



15,000 h



Non-dimmable



50,000+



Shape

### Lamp type – plastic

	LED (W)	CCT (K)	Light output (lm)	Replacement-wattage (W)	Dimension w × h (mm)	EAN1	12NC
PILA LED 40W P45 E14 WW FR ND 1CT/10	4.9	2700	470	40	45 × 88	8727900972153	929003540531
PILA LED 40W P45 E27 WW FR ND 1CT/10	4.9	2700	470	40	45 × 88	8727900972177	929003540631
PILA LED 40W P45 E14 4000K FR ND	4.9	4000	470	40	45 × 88	8727900972771	929003540731
PILA LED 40W P45 E27 4000K FR ND	4.9	4000	470	40	45 × 88	8727900972757	929003540831



CRI



15,000 h



Non-dimmable



50,000+



Shape

### Lamp type – glass

	LED (W)	CCT (K)	Light output (lm)	Replacement-wattage (W)	Dimension w × h (mm)	EAN1	12NC
PILA LED CLA 25W P45 E14 WW CL ND 1CT/10	2	2700	250	25	80 × 45	8727900966268	929001238631
PILA LED CLA 40W P45 E14 WW CL ND 1CT/10	4.3	2700	470	40	80 × 45	8727900966305	929001890431
PILA LEDCLA 60W P45 E14 WW CL ND 1CT/10	6.5	2700	806	60	80 × 45	8727900970548	929003036131



# PILA LED spots

## Benefits

- Up to 90% energy savings compared with halogen lamps
- Low maintenance costs
- Low initial investment
- Reliable quality



CRI



15,000 h



Non-dimmable



30,000+



Cap

Lamp type – plastic	LED (W)	CCT (K)	Light output (lm)	Replacement-wattage (W)	Beam angle (°)	Dimension w × h (mm)	EAN1	12NC
PILA LED 40W P45 E14 WW FR ND 1CT/10	3	2700	250	35	36	50 × 56	8727900970500	929003038531
PILA LED 40W P45 E27 WW FR ND 1CT/10	3	4000	280	35	36	50 × 56	8727900970487	929003038231
PILA LED 50W GU10 WW 36D ND 1CT/10	4.7	2700	400	50	36	50 × 56	8727900970449	929003038631
PILA LED 50W GU10 CW 36D ND 1CT/10	4.7	4000	460	50	36	50 × 56	8727900970425	929003038331
PILA LED 50W GU10 827 36D ND 3CT/6	4.7	2700	400	50	36	50 × 56	8727900971774	929003038651
PILA LED 50W GU10 840 36D ND 3CT/6	4.7	4000	430	50	36	50 × 56	8727900971750	929003038351
PILA LED 65W GU10 WW 36D ND 1CT/10	4.9	2700	460	65	36	50 × 56	8727900970609	929003038831
PILA LED 65W GU10 CW 36D ND 1CT/10	4.9	4000	460	65	60	50 × 56	8727900964615	929001371231
PILA LED 50W GU10 CW 60D ND 1CT/10	4.7	4000	430	50	120	50 × 58	8718696537015	929001912331
PILA LED GU10 350lm 120D 2700K ND	4	2700	350	32	120	50 × 58	8727900972573	929003597531
PILA LED GU10 350lm 120D 4000K ND	4	4000	350	32	120	50 × 58	8727900972658	929001358541
PILA LED 500lm GU10 WW120D ND 1CT/10	4.9	2700	500	42	120	50 × 58	8727900965254	929001372031
PILA LED 500lm GU10 CW120D ND 1CT/10	4.9	4000	500	42	120	50 × 58	8727900965230	929001358631
PILA LED 500lm GU10 827 120D ND 3CT/6	4.9	2700	500	42	120	50 × 58	8727900972412	929001372051
PILA LED 500lm GU10 840 120D ND 3CT/6	4.9	4000	500	42	120	50 × 58	8727900972436	929001358651
PILA LED GU10 720lm 120D 2700K ND	7	2700	720	54	120	50 × 58	8727900972535	929003597431
PILA LED GU10 720lm 120D 4000K ND	7	4000	720	54	120	50 × 58	8727900972559	929002093431



# PILA LED bulbs

## Benefits

- Up to 90% energy savings compared with traditional incandescent lamps
- Low maintenance costs
- Low initial investment
- Reliable quality



Lamp type – plastic	LED (W)	CCT (K)	Light output (lm)	Replacement-wattage (W)	Dimension w × h (mm)	EAN1	12NC
PILA LED 40W A60 E27 WW FR ND 1CT/6	4.9	2700	470	40	60 × 108	8727900968569	929003540251
PILA LED 40W A60 E27 CW FR ND 1CT/6	4.9	4000	470	40	60 × 108	8727900968927	929003564131
PILA LED 60W A60 E27 WW FR ND 1CT/6	8	2700	806	60	60 × 108	8727900968521	929002306231
PILA LED 60W A60 E27 CW FR ND 1CT/6	8	4000	806	60	60 × 108	8727900968606	929002306331
PILA LED 60W A60 E27 865 FR ND 1CT/10	8	6500	806	60	60 × 108	8727900971798	929002306451
PILA LED 60W A60 E27 840 FR ND 3CT/6	8	4000	806	60	60 × 108	8727900972450	929002306352
PILA LED 75W A60 E27 WW FR ND 1CT/6 G3	10	2700	1055	75	60 × 108	8727900968620	929002306531
PILA LED 75W A60 E27 CW FR ND 1CT/6 G3	10	4000	1055	75	60 × 108	8727900968644	929002306631
PILA LED 75W A60 E27 CDL FR ND 1CT/6	10	6500	1055	75	60 × 108	8727900968668	929002306731
PILA LED 75W A60 E27 840 FR ND 3CT/6	10	4000	1055	75	60 × 108	8727900972375	929002306651
PILA LED 100W A60 E27 WW FR ND 1CT/6	13	2700	1521	100	60 × 120	8727900968682	929002306831
PILA LED 100W A60 E27 CW FR ND 1CT/6 G3	13	4000	1521	100	60 × 120	8727900968507	929002306931
PILA LED 100W A60 E27 840 FR ND 3CT/6	13	4000	1521	100	60 × 120	8727900972399	929002306951
PILA LED 120W A67 E27 WW FR ND 1CT/6	15	2700	1900	120	68 × 128	8727900967142	929002062231
PILA LED 120W A67 E27 4000K FR ND	15	4000	1900	120	68 × 128	8727900972818	929003112931
PILA LED 150W A80 E27 2700K FR ND	23	2700	2500	150	80 × 155	8727900972474	929003597131
PILA LED 150W A80 E27 4000K FR ND	23	4000	2500	150	80 × 155	8727900972498	929003597231
Lamp type – glass	LED (W)	CCT (K)	Light output (lm)	Replacement-wattage (W)	Dimension w × h (mm)	EAN1	12NC
PILA LED CLA40W A60 E27 WWND 1CT/10	4.5	2700	470	40	60 × 104	8727900963915	929001242972
PILA LED CLA 40W A60 E27 WW CL ND 1CT/10	4.3	2700	470	40	60 × 104	8727900966244	929001890031
PILA LED CLA60W A60 E27 WWND 1CT/10	7	2700	806	60	60 × 104	8727900970524	929003033331
PILA LED CLA 60W A60 E27 WW CL ND 1CT/10	7	2700	806	60	60 × 104	8727900970364	929003033931
PILA LED CLA 75W A60 E27 WW CL ND 1CT/6	8.5	2700	1055	75	60 × 104	8727900970340	929003033831
PILA LED CLA 100W A60 E27 WW CL ND 1CT/6	10.5	2700	1521	100	60 × 104	8727900968545	929002026131

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.



# PILA LED candles

## Benefits

- Up to 90% energy savings compared with traditional incandescent lamps
- Low maintenance costs
- Low initial investment
- Reliable quality



CRI



15,000 h



Non-dimmable



30,000+



Shape

### Lamp type – plastic

	LED (W)	CCT (K)	Light output (lm)	Replacement-wattage (W)	Dimension w × h (mm)	EAN1	12NC
PILA LED 25W B35 E14 WW FR ND 1CT/10	3	2700	250	25	35 × 106	8727900970388	929002966831
PILA LED 40W B35 E14 WW FR ND 1CT/10	4.9	2700	470	40	35 × 106	8727900970401	929003541151
PILA LED 40W B35 E14 4000K FR ND	4.9	4000	470	40	35 × 106	8727900972733	929003604031
PILA LED 60W B35 E14 WW ND 1CT/10	8	2700	806	60	38 × 114	8727900970241	929002972531
PILA LED 60W B35 E14 CW ND 1CT/10	8	4000	806	60	38 × 114	8727900970265	929002972731
PILA LED 60W B35 E14 CDL ND 1CT/10	8	6500	806	60	38 × 114	8727900970289	929002972931



CRI



15,000 h



Non-dimmable



20,000+



Shape

### Lamp type – glass

	LED (W)	CCT (K)	Light output (lm)	Replacement-wattage (W)	Dimension w × h (mm)	EAN1	12NC
PILA LED CLA 25W B35 E14 WW CL ND 1CT/10	2	2700	250	25	97 × 35	8727900966206	929001238331
PILA LED CLA 40W B35 E14 WW CL ND 1CT/10	4.3	2700	470	40	97 × 35	8727900966220	929001889731
PILA LEDCLA 60W B35 E14 WW CL ND 1CT/10	6.5	2700	806	60	97 × 35	8727900970302	929003035931