

# LED G25

## 4.5G25/VIN/820/E26/CL/GL/DIM 4/FBH T20

Philips G25 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.


### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	4.5-40W
Light Technical	
Color Code	820 [ CCT of 2000K]
Initial lumen (Nom)	300 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	66.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	4.5 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)		0.7
Voltage (Nom)		120 V
Temperature		
T-Case Maximum (Nom)		50 °C
Controls and Dimming		
Dimmable		Yes
Mechanical and Housing		
Bulb Finish		Amber
Approval and Application		
Energy Efficiency Label (EEL)		Not applicable
Energy Consumption kWh/1000 h		- kWh
Product Data		
Order product name		4.5G25/VIN/820/E26/CL/GL/DIM 4/FBH T20
EAN/UPC - Product		046677556815
Order code		556811
Numerator - Quantity Per Pack		1
Numerator - Packs per outer box		4
Material Nr. (12NC)		929001951233
Net Weight (Piece)		0.030 kg

LED G25


Dimensional drawing




Bulb G25 4.5-40W 300lm 2000K E26 D Amber

Product	D	C
4.5G25/VIN/820/E26/CL/GL/DIM 4/FBH T20	80 mm	119 mm


Photometric data



LEDbulb 4,5W G25 E26 820 Amber



LEDbulb 4,5W G25 E26 820 Amber



LEDbulb G25 4,5W E26 820 Amber

LED G25

Lifetime



15K LED



15K LMP

