



## A vision of versatility

**Lumec OmniScape LED Post Top & Arm Mount** luminaires offer a clean and modern aesthetic while providing a foundation to build your vision and enhance any outdoor space. Along with providing uniquely customizable design flexibility and personalization, these luminaires deliver industry leading performance. This new family also allows for the integration of connected ready controls and technology.

### Modularity

#### Custom combinations

- Contemporary style
- Transitional style
- Historical style
- Post top mount
- Arm mount
- Skirt option & finial options
- LEDgine/ComfortEdge™ light engines
- 2700, 3000, 4000K CCT in 70/80 CRI
- Multiple distributions available
- 5-year limited warranty  
(for more info visit [signify.com/warranties](http://signify.com/warranties))

### Performance

#### LEDgine

- Post top: Up to 18,000lm (169 LPW)
- Arm mount: Up to 21,000lm (198 LPW)

#### ComfortEdge™

- Post top: Up to 16,000lm (132 LPW)
- Arm mount: Up to 18,000lm (152 LPW)

### Connectivity

#### Connected ready options & controls

- Zhaga certified driver (zD4i)
- Digitally addressable lighting interface driver (DALI)
- Sensor Ready driver (SR)
- 7-pin receptacle (TRLD7)
- Zhaga socket (TLRSR)
- Outdoor Multi-Sensor (OMS)
- Microwave Motion Sensors (MW)
- Field Adjustable Watt Selector (FAWS)
- Photoelectric Cell controls (PH)

# OSA/OSP OmniScape

## LED Arm Mount



S-OSAOSC 2  
Contemporary  
dual arm bracket


S-OSAOSC 1A  
Contemporary  
single arm bracket



S-OSAOST 2  
Transitional  
dual arm bracket

S-OSAOST 1A  
Transitional  
single arm bracket

Mix components to create your own personal style and accentuate any outdoor space. OmniScape is designed to meet a broad range of Contemporary, Transitional or Historical lighting applications in a single family.



Finials (optional)

Contemporary roof

Transitional roof

Historical roof

### Contemporary

#### Boasting a modern and refined aesthetic

This style incorporates a minimalist design language and soft volume transitions. Distinctively modern and aimed at contemporary architectural spaces, yet the minimalist appearance makes it suitable for a variety of outdoor areas.

### Transitional

#### Fusion of classic and modern elements

This style creates a sophisticated and elegant look. Inspired by the natural beauty of the calla lily, and flow seamlessly from the base to the light source. The design is adaptable and timeless, complementing any architectural style or outdoor setting.

### Historical

#### Past inspirations blended into present

The top section combines dome and cornice forms to add character and familiarity to the design. Optional fitter styles for the roof create a smooth and elegant classic silhouette. The design is suitable for both historical and modern settings, as it blends the past and the present in a versatile way.



S-OSAC  
Contemporary Roof

S-OSAT  
Transitional Roof

S-OSAH  
Transitional Roof shown with optional finial

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

**GENLYTE SOLUTIONS**  
a signify business

Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.