

Track MS Series

Illuminate with Precision

This stylish track head delivers the accented light your space needs. The MS Series Track Head features AccuRender Technology (CRI 90), ensuring colors are rendered more accurately and consistently, while doing so as efficiently as CRI 80 products.

Using bio-circular polycarbonate materials, the MS Series offers a range of colors, textures, and lumen packages up to 2300lm. Its specification grade optics with strong Center Beam Candle Power result in amazing performance, making it the perfect option for your retail, hospitality or office spaces.

[Configuration](#)

[Downloads](#)


Application Imagery



Key specifications

- Configurable with 3 adapter types, 7 colors, and 4 beams
- 1000-2300 lumens
- efficacy up to 111 lm/W
- Standard CRI 90 with 2700K, 3000K, 3500K, and 4000K CCT options
- ELV dimming
- Declare Label - LBC Red List Approved
- DLC Premium
- Lifetime L90B50 at 65,000 hours
- Printed and Assembled in Littlestown PA
- Buy American Act (BAA) Compliant

Schematic light drawing



Operational & certifications

Protection Class	IP20
Ambient Range	0 to +25C
Certifications	cULus, RoHS and Declare. DLC Premium
Warranty	5 Years

Electrical

Dimming: ELV
Input Voltage: 120V
Frequency: 50/60Hz
Power Factor: 0.9

[Configuration](#)

Downloads

- [3D printing Brochure](#)
- [Spec Sheet](#)
- [Photometrics - 16" Low Bay - BAL Series](#)
- [Photometrics - 12" Low Bay - BAL S Series](#)
- [Mounting instruction](#)

Interested?

Learn more about possibilities offered by 3D-printed luminaries.

- [Sustainability](#) >
- [Co-Creation](#) >
- [Our Products](#) >
- [Applications](#) >

LIGHTOLIER