

PHILIPS

LED lamps

FlexFit selectable TLED



Three is really a charm

Philips TLED FlexFit (Type A+B) T8 color selectable lamps take flexible installation to a whole new level with CCT selectable and 3 installation options. The lamp can be installed as a plug-and-play (UL Type A), a double-ended or single-ended ballast bypass (UL Type B). Combined with the ability to select one of five color temperatures and a single FlexFit lamp can take the place of 15 standard lamps.

Benefits

- **One lamp, 15 solutions**
5 CCTs, 3 installation methods
- **One lamp, 5 colors**
Use the switch to select one of 5 CCTs (3000, 3500, 4000, 5000 & 6500K)
- **Lifetime Delivered**
Average life rating of 50,000 hrs²
- **Reduced warehousing**
Uses 97% less warehouse space than carrying individual lamps³

Features

- **Full-length illumination**
Maximize illumination with small end-caps
- **Light quality and performance**
Predictability delivers consistent light output with no flicker
- **Proven, reliable**
Brand with over 120-year history
- **Available in 3 lengths**
2ft, 3ft & 4ft

1. For proper operation shunting of un-shunted sockets is required. See installation guide for details

2. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70).

3. Savings based on reducing 15 SKUs to 1

Philips FlexFit selectable TLED lamps


Ordering, electrical and technical data (Subject to change without notice)

G13


Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	DLC ID	MIL (in)	Beam Angle	Pkg Qty
Philips FlexFit selectable TLED lamps												
588624	929003794504	7.5T8/COR/24-5CCT/FF11/G/DIM 25/1	7.5	1100	120-277V	82		50000	S-KG25BR	24	240	25
588632	929003794604	10.5T8/COR/36-5CCT/FF15/G/DIM 25/1	10.5	1500	120-277V	82	3000/3500/4000/5000/6500	50000	S-V0S96M	36	240	25
588640	929003794704	12T8/COR/48-5CCT/FF18/G/DIM 25/1	12	1800	120-277V	82		50000	S-SR7DNJ	48	240	25

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.

Installation Flexibility



Design highlights



- FlexFit TLEDs exceed UL pin leakage requirements of <5 M.I.U.
- Blue end-cap = Type A. Grey stripe = Type B Installation.
- Tested per IEEE 1789-2015. SVM <1.0 is negligible.

For more info on Philips' limited warranty please visit www.philips.com/warranties.



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corp.
400 Crossing Boulevard,
Bridgewater, NJ 08807
Telephone 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.