

PHILIPS

Compact fluorescent
Spiral bulb

Spiral

23 W (100 W)

Medium base (E26)

Daylight

046677416010



Spend a little, save a lot

Philips Twister Mini energy-saving bulbs provide instant brightness and make colors appear more vivid. Due to its compact design, this low-consumption spiral bulb is ideal for narrow luminaires, saving energy and money for up to 10 years.

Sustainable choice

- Lasts up to 9 years
- Very low energy consumption; saving at least 77%

Energy efficiency

- An energy saving twister lamp, it can last up to 10,000 hrs

Similar to Incandescent

- Similar to Incandescent

MultiPack

- Offered in a convenient 4-pack for even more savings

Bring your room to life

- This twister bulb simulates natural daylight

Highlights

Lifetime 9 years

With a lifetime of up to 10,000 hours, this Philips CFL lamp will ensure your desired atmosphere for up to 9 years*.

Saving up to 77%

By replacing traditional light bulbs with a Philips CFL alternative, you will gain immediate, significant, energy savings while contributing to a sustainable planet.

Energy efficient lamp

This bulb saves up to \$84.70 in energy costs when you replace a 100 Watt incandescent with this 23 Watt compact fluorescent light bulb**.

Similar to Incandescent

This CFL lamp is perfect for general lighting. Ideal for table lamps and wall sconces.

Multi Pack

A convenient 4-pack for even more savings

Daylight 6500K

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low value produce a warm, more cozy light, while those with a high Kelvin value, create a cool, more energizing light.

Specifications

Bulb characteristics

- Shape: Spiral
- Socket: E26
- Lamp shape code: Mini Twister
- Dimmable: No

Bulb dimensions

- Height: 139 mm
- Width: 132 mm

Durability

- Average life (at 2.7 hrs/day): 9 year(s)
- Nominal lifetime: 10,000 hour(s)

Light characteristics

- Application: Extra brightness
- Color temperature: 6500 K
- Light Color Category: Daylight
- Nominal luminous flux: 1600 lm

Power consumption

- Wattage: 23 W
- Wattage equivalent: 100 W

Rated values

- Rated lifetime: 10,000 hour(s)
- Rated luminous flux: 1600 lm

Packaging dimensions and weight

- EAN/UPC - product: 046677416010
- Net weight: 0.31 kg
- Gross weight: 0.47 kg
- Height: 12.3 cm
- Length: 27.4 cm
- Width: 6.9 cm
- Material number (12NC): 929689750003



Issue date: 2024-09-08
Version: 0.539

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com