

PHILIPS

Bulb 60W A19 E26
x6

LED

2700K

800lm

11000h

046677455590



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Long life bulb - Lasts up to 10 years

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Dimmable: No
- Bulb Finish: Frosted

Bulb dimensions

- Height: 10.4 cm
- Width: 6 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 11,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 827 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Flux: 800 lm
- Luminous Efficacy (rated) (Nom): 88.00 lm/W

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 88 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 046677455590
- EOC: 455592
- Product title: 9A19/LED/827/FR/P/ND 4/6FB

Power

- Power Factor (Fraction): 0.5

Power consumption

- Power factor: 0.5
- Voltage: 120 V
- Wattage: 9 W
- Wattage equivalent: 60 W
- Power Consumption: 9 W

Product dimensions and weight

- Length: 10.4 cm

Rated values

- Rated lifetime: 11,000 hour(s)

Technical specifications

- Frequency: 60 Hz
- Line Frequency: 60 Hz
- Dimmable: No
- Cap-Base: E26 | Single Contact
Medium Screw

Packaging dimensions and weight

[9A19/LED/827/FR/P/ND 4/6FB]

- EAN/UPC - product: 046677455590
- Net weight: 0.28 kg
- Gross weight: 0.37 kg
- Height: 11.5 cm
- Length: 12.5 cm
- Width: 18.7 cm
- Material number (12NC):
929002311375

Packaging dimensions and weight

[9A19/LED/927/FR/P/E26/ND 4/6CT]

- EAN/UPC - product: 046677455590
- Net weight: 0.21 kg
- Gross weight: 0.38 kg
- Height: 11.5 cm
- Length: 12.5 cm
- Width: 18.7 cm
- Material number (12NC):
929003004875



Issue date: 2024-06-19
Version: 0.31

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com