

# PHILIPS

Bulb

LED

8W (60W)

E26

Yellow

046677463250



## Brighten your home with infinite possibilities.

Philips LED energy-saving colored bulbs provide instant brightness and make colors appear more vivid. Ideal for special activities and occasions.

### High quality light

- Designed for the comfort of your eyes

### Saves up to 80% energy

- Saves up to 80% energy

### Instant on

- Instant light when switched on

### Light beyond illumination

- Deep Color Saturation

# Highlights

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

## Instant On



No need to wait: Philips LED light bulbs provide their full level of brightness immediately when they are switched on. Just by flipping the switch, your room is at full brightness. There is no slow starting or waiting.

## Brilliant Colors

Philips colored LED bulbs achieve deep color saturation to make the most of your festive atmosphere

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

## Bulb dimensions

- Height: 10.7 cm
- Width: 6 cm

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 10,950 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

**Light characteristics**

- Beam angle: 160 degree(s)
- Color rendering index (CRI): -
- Warm-up time to 60% light: 0.5 s

**Miscellaneous**

- EyeComfort: Yes
- LED Innovations: EyeComfort

**Other characteristics**

- EU RoHS compliant: Yes

**Packaging information**

- EAN: 046677463250
- EOC: 463257
- Product title: 8A19/LED/  
YELLOW/P/ND 120V 4/1FB

**Power**

- Power Factor (Fraction): 0.5

**Power consumption**

- Power factor: 0.5
- Voltage: 120 V
- Wattage: 8 W
- Power Consumption: 8 W

**Product dimensions and weight**

- Length: 10.7 cm

**Rated values**

- Rated lifetime: 10,950 hour(s)

**Technical specifications**

- Frequency: 60 Hz
- Line Frequency: 60 Hz
- Dimmable: No
- Cap-Base: E26 | Single Contact  
Medium Screw

**Packaging dimensions and weight**

- EAN/UPC – product: 046677463250
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 10.7 cm
- Length: 6.2 cm
- Width: 6.2 cm



Issue date: 2025-03-18  
Version: 0.550

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)