

PHILIPS

LEDtube Type A T5

LED

1200mm

3000/4000/5000K

G5

046677580223



Bright LED lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. Select desired color temperature via switch before installing the LED tube.

Choose a simple replacement for your old bulbs

- Compatible with most instant-start electronic ballasts

Choose for a sustainable solution

- Long life bulb - Lasts up to 50 years

Highlights

InstantFit Ballast Compatibility

Philips InstantFit LED tubes have been tested and operated to work on more ballast types than competitive products in the market. Check the compatibility list here (link to <http://images.philips.com/is/content/>)

PhilipsConsumer/PDFDownloads/United%20States/ODLI20180301_001-UPD-en_US-PLT-16118CR_InstantFit_Ballast-Compatibility-Guide_2018-1.pdf)

Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: T5
- Socket: G5
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: Yes - Check ballast compatibility
- Bulb Material: Glass

Bulb dimensions

- Height: 116.3 cm
- Width: 1.86 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000/4000/5000 K
- Nominal luminous flux: 3100, 3300, 3300 lm
- Warm-up time to 60% light: instant full light
- Color Code: 3000K/4000K/5000K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

- Efficacy: 137 lm/W

Packaging information

- EAN: 046677580223
- EOC: 580225
- Product title: 24T5HO/LED/46-3CCT/IF33/G/DIM 10/1 FB

Power consumption

- Power factor: 0.9
- Voltage: 39-64 V
- Wattage: 24 W
- Wattage equivalent: 54 W

Product dimensions and weight

- Length: 116.3 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Frequency: VA51018828 Hz

046677580223

Packaging dimensions and weight

- EAN/UPC - product: 046677580223
- Net weight: 0.15 kg
- Gross weight: 0.23 kg
- Height: 117.5 cm
- Length: 2.5 cm
- Width: 2.5 cm



Issue date: 2024-11-21
Version: 0.47

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com