

# PHILIPS

Filament Bulb Frosted  
100W A19 E26

LED

2200-2700K

1500lm

15000h

Dimming

046677587048



## Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

### High quality light

- Designed for the comfort of your eyes

### Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Specifications

## Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: Only with specific dimmers
- Bulb Material: Glass

## Bulb dimensions

- Height: 10.5 cm
- Width: 6 cm

## Design and finishing

- Material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 2200-2700 K
- Nominal luminous flux: 1500 lm

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

## Other characteristics

- Efficacy: 130 lm/W

## Packaging information

- EAN: 046677587048
- EOC: 587048
- Product title: 11.5A19/PER/UD/FR/G/E26/WGD 4/1PF T20

## Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 11.5 W
- Wattage equivalent: 100 W

## Product dimensions and weight

- Length: 10.5 cm

046677587048

#### Rated values

- Rated peak intensity: 130 cd

#### Technical specifications

- Frequency: 60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 046677587048
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 17.1 cm
- Length: 7.5 cm
- Width: 6.5 cm



Issue date: 2024-11-21  
Version: 0.120

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)