

PHILIPS

Filament Bulb Frosted
100W A19 E26

LED

3000K

1500lm

15000h

Dimming

046677587062



Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Create the right light for your home

- Perfect for general room lighting

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces standard incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving standard LED bulb. The perfect sustainable replacement for traditional standard incandescent bulbs.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Specifications

Bulb characteristics

- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Frosted
- Dimmable: Only with specific dimmers
- Bulb Finish: Frosted
- Bulb Material: Glass

Bulb dimensions

- Height: 10.5 cm
- Width: 6 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 3000 K
- Nominal luminous flux: 1500 lm

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

Other characteristics

- Efficacy: 130 lm/W

Packaging information

- EAN: 046677587062
- EOC: 587063
- Product title: 11.5A19/PER/
UD30/FR/G/E26/D 4/1PFT20

Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 11.5 W
- Wattage equivalent: 100 W

Product dimensions and weight

- Length: 10.5 cm

Rated values

- Rated peak intensity: 130 cd

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677587062
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 17.1 cm
- Length: 7.5 cm
- Width: 6.5 cm



Issue date: 2025-02-21
Version: 0.121

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com