

# PHILIPS

Bulb (Dimmable)

LED

4.5W-65W

E26

Daylight

Dimming

046677589004



## UltraEfficient lamp, provide most sustainable and energy saving solution for you

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### Choose for a sustainable solution

- Long life bulb - Lasts up to 50 years

### Light beyond illumination

- Dimmable

# Highlights

## Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be

certain that your particular dimmer can be used with this bulb.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Dimmable: Only with specific dimmers
- Bulb Finish: Frosted
- Bulb Material: Plastic

## Bulb dimensions

- Height: 13 cm
- Width: 9.4 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Nominal luminous flux: 650 lm

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 144 lm/W

## Packaging information

- EAN: 046677589004
- EOC: 589002
- Product title: 4.5BR30/UE/950/P/E26/D/T20 4/1PF SRP

## Power consumption

- Power factor: 0.7
- Voltage: AC 120 V
- Wattage: 4.5 W
- Wattage equivalent: 65 W

## Product dimensions and weight

- Length: 13 cm

## Technical specifications

- Frequency: 60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 046677589004
- Net weight: 0.07 kg
- Gross weight: 0.11 kg
- Height: 20.9 cm
- Length: 9.5 cm
- Width: 13 cm



Issue date: 2024-11-21  
Version: 0.86

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)