

# PHILIPS

Parterre Wall Light  
7.5W

myGarden


2700K

Black

Water Resistant



16480/30/P0



## Enjoy a beautiful garden with light

The Philips Parterre LED black outdoor wall light suspends a cube of light within a durable die-cast aluminium cradle. The ingenious design catches the eye, and casts beams of warm white light in all directions on your wall.

### Sustainable light solutions

- High quality LED light

### Special characteristics

- Weather-proof

# Highlights

## High quality LED light

The LED light bulb delivered with this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

## Weather-proof



This Philips outdoor lamp is specially designed for humid outdoor

environments and has undergone rigorous tests to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This lamp is designed with IP44: it is protected against splashing water. This product is most common and ideal for general outdoor use.

# Specifications

## Design and finishing

- Colour: Black
- Material: Aluminium

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: Yes

## Garden area

- Garden area: Garden and Patio

## Miscellaneous

- Especially designed for: Garden and Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Water Resistant

## Product dimensions and weight

- Net weight: 0.660 kg
- Height: 13 cm
- Length: 13 cm
- Width: 13 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 25,000 h
- Total lumen output fixture: 800 lm
- Mains power: 50 Hz
- LED: Yes
- Energy class included light source: F
- Wattage bulb included: 8 W
- IP code: IP44
- Class of protection: Class II
- Light source replaceable: No
- Number of light sources: 1

## Packaging dimensions and weight

- EAN/UPC - product: 8718696158838
- Net weight: 0.66 kg
- Gross weight: 0.75 kg
- Height: 14.6 cm
- Length: 13.6 cm
- Width: 13.6 cm



Issue date: 2024-11-21  
Version: 0.484

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)