

PHILIPS

Limbali Ceiling/Wall
Spotlight 4x

Ceiling/Wall Spotlights

No bulb

Nickel



8718696133224



The accent on style

Include this practical Philips spotlight in your home. Choose your Philips GU10 LED bulb to go with your spot style and ensure a high-quality and long-lasting light.

Ease of use

- Adjustable spot head
- No bulb included

Premium quality

- Long-lasting, high-quality materials

Special characteristics

- For any room in your interior

Highlights

Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

No bulb included

This luminaire comes without a bulb, which enables you to choose the light output which is best suited to the room and your personal taste. Choosing a Philips LED bulb will ensure a high quality and long-lasting light output.

Long-lasting, high-quality materials

This spot light is made of long-lasting, high-quality materials with superior finishing. This ensures a solid and durable product that will enhance and light up your home for many years to come.

For any room in your interior

Fully functional and at the same time very elegant, this Philips spotlight will bring a decorative touch to any room in your home.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: Nickel
- Material: Metal

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Yes
- Dimmable with remote control: No
- Remote control included: No

Light characteristics

- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Hallway
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: No

Product dimensions and weight

- Net weight: 0.51 kg
- Height: 13 cm
- Length: 69 cm
- Width: 8 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: No bulb included
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: No
- Fitting/cap: GU10
- Wattage bulb included: 50W
- Maximum wattage replacement bulb: 50 W
- IP code: IP20
- Class of protection: Class I
- Light source replaceable: Yes
- Number of light sources: 4

8718696133224

Packaging dimensions and weight

- EAN/UPC - product: 8718696133224
- Net weight: 0.5 kg
- Gross weight: 0.72 kg
- Height: 70 cm
- Length: 9 cm
- Width: 10 cm



Issue date: 2025-02-17
Version: 0.206

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com