

PHILIPS

Donegal Recessed
Light

Recessed Lights

No bulb

Copper & brass

8718696160930



Create the right light style

Philips Donegal recessed spot light is made of premium, no dust, no rust material for effortless maintenance. Choose your Philips GU10 LED bulb to go with your spot style and ensure a high-quality and long-lasting light.

Ease of use

- Adjustable spot head

Designed for your living room and bedroom

- No dust, no rust

Premium quality

- Easy to clean

Highlights

Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

Easy to clean

Smooth and easy-to-clean materials mean your home always looks attractive from floor to ceiling.

No dust, no rust

The special no dust, no rust surface material of this recessed spot minimises dust-gathering and ensures a long lifetime for your product.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: Copper and Brass
- Material: Synthetic

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: No
- Remote control included: No

Light characteristics

- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: No

Product dimensions and weight

- Net weight: 0.248 kg
- Cut out length: 7.0 cm
- Cut out width: 7.0 cm
- Height: 4 cm
- Length: 9 cm
- Width: 9 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Mains power: AC 220-240
- Fixture dimmable: Yes
- LED: Yes
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8718696160930
- Net weight: 0.25 kg
- Gross weight: 0.36 kg
- Height: 308 mm
- Length: 103 mm
- Width: 53 mm



Issue date: 2024-11-21
Version: 0.191

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com