

PHILIPS

Bulb

LED

40 W

E27

8718696167779



Complete the classic look

This Philips classic cord combines a fabric wire and metal socket with classic finishing to bring a classic vibe to your living space. Paired with an E27 LED lamp from the Philips classic range to complete the look

Designed for your living room and bedroom

- High quality material
- Adjustable cable length

Choose a simple replacement for your old lamps

- Cord

Highlights

High quality material [Cable]

This beautiful fabric covered cable ensures that your lamp hangs straight when installed. The matt satin finish of the metal socket enhances the antique look of any bulb.

Adjustable cable length [Cable]

Cable is fully adjustable for various heights giving the flexibility to arrange a stylish dynamic combination of suspension lighting above your kitchen island and dining table.

Cord

This Philips lamp can be used in combination with one of the Philips cords to complete your interior illumination and bring an industrial feel to your living space.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Accessory
- Socket: E27
- Dimmable: No

Durability

- Lumen maintenance factor: 70%
- Number of switch cycles: 25,000
- Nominal lifetime: 10,950 h

Light characteristics

- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 0.00 lm/W

Miscellaneous

- Extra Features: Decorative

Other characteristics

- Lamp current: 330 mA
- Efficacy: 0 lm/W
- CE mark: Yes
- EU RoHS compliant: Yes

Power consumption

- Power factor: 0.5
- Voltage: 120-240 V
- Wattage: 40 W
- Power Consumption: 40 W

Product dimensions and weight

- Length: 10.7 cm

Rated values

- Rated power: 40 W

Technical specifications

- Frequency: 50-60 Hz
- Line Frequency: 50 to 60 Hz
- Cap base: E27

Packaging dimensions and weight

- EAN/UPC - product: 8718696167779
- Net weight: 0.43 kg
- Gross weight: 0.48 kg
- Height: 16.9 cm
- Length: 7.1 cm
- Width: 16.9 cm
- Material number (12NC): 929001978001



Issue date: 2024-09-16
Version: 0.975

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com