

PHILIPS

Filament Bulb Clear
60W G93 E27

LED

2700K


806 lm

15000 h

Non-dimmable



8718696742457



A light bulb like no other

Familiar shapes that you know and love. They provide you with the classic look of incandescent lamps, while using around 80% less energy. The wide beam angle enables a perfect, all-around distribution of the light.

High-quality light

- Designed for the comfort of your eyes

Create the right light for your home

- Perfect for general room lighting

Light beyond illumination

- Vintage style, modern LED technology

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Vintage-style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Specifications

Bulb characteristics

- Shape: Globe
- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Type of glass: Clear
- Dimmable: No
- Lamp Finish: Clear
- Bulb Material: Glass

Lamp dimensions

- Height: 14 cm
- Width: 9.5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Colour Temperature (Nom): 2700 K
- Luminous Flux: 806 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 115.00 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- Efficacy: 115 lm/W
- EU RoHS compliant: Yes

Packaging information

- Product family: LED Classic, EyeComfort
- EAN: 8718696742457
- EOC: 871869674245700
- Product title: LED classic 60W G93 E27 WW CL ND 1PF

Power

- Power Factor (Fraction): 0.51

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage: 7 W
- Wattage equivalent: 60 W
- Power Consumption: 7 W
- Energy efficiency label (EEL): E

Product dimensions and weight

- Length: 14 cm

Rated values

- Rated lifetime: 15,000 h

Technical specifications

- Frequency: 50–60 Hz
- EPREL Registration Number: 1825194
- Flux measurement reference: Sphere
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60 Hz
- Dimmable: No
- Cap base: E27

Packaging dimensions and weight

- EAN/UPC – product: 8718696742457
- Net weight: 0.07 kg
- Gross weight: 0.15 kg
- Height: 19.5 cm
- Length: 10.4 cm
- Width: 10.4 cm



Issue date: 2025-01-14
Version: 0.729

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com