

# PHILIPS

Filament Candle Clear  
40W B35 E14 x6

LED

2700K


470 lm

15000 h

Non-dimmable



8718696775035



## Clear LED candle bulbs add a sparkle to your home

Familiar shapes you know and love. They provide you with the classic look of the incandescent lamps, while using around 80% less energy. The wide beam angle enables a perfect, all-around distribution of the light.

### High-quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Better for your wallet and your planet

### Create the right light for your home

- Perfect for general room lighting

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

### Energy savings of up to 90%

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

## Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E14
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Lamp dimensions

- Height: 9.7 cm
- Width: 3.5 cm

## Design and finishing

- Material: Glass

## Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Other characteristics

- Efficacy: 109 lm/W

## Packaging information

- EAN: 8718696775035
- EOC: 871869677503501
- Product title: LEDclassic 40W B35 E14 WW CL ND 6CT/4 UK

## Power consumption

- Power factor: 0.41
- Voltage: 220-240 V
- Wattage: 4.3 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): F

## Product dimensions and weight

- Length: 9.7 cm

#### Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 387402

#### Packaging dimensions and weight

- EAN/UPC - product: 8718696775035
- Net weight: 0.09 kg
- Gross weight: 0.16 kg
- Height: 11.5 cm
- Length: 6.3 cm
- Width: 17.1 cm
- Material number (12NC):  
929001889795



Issue date: 2024-07-25  
Version: 0.1136

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)