

PHILIPS

Spot 50W PAR16
GU10 x10

LED

2700K

355 lm

15000 h



8718696778265



It's what's inside that makes the difference

With its beautifully shaped design and familiar dimensions, this LED spot is the perfect sustainable replacement for a traditional halogen spot.

High-quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old lamps

- Similar shape and size to standard halogen bulb

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces standard halogen



With its beautifully shaped design and familiar dimensions, this is a modern lighting energy-saving, standard, LED bulb. The perfect sustainable replacement for traditional standard halogen bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Lamp dimensions

- Height: 5.4 cm
- Width: 5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 355 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

Other characteristics

- Efficacy: 77 lm/W

Packaging information

- EAN: 8718696778265
- EOC: 871869677826501
- Product title: LEDClassic 50W GU10 WW 36D ND 10PK UK

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 4.6 W
- Wattage equivalent: 50 W
- Energy efficiency label (EEL): F

Product dimensions and weight

- Length: 5.4 cm

Rated values

- Rated peak intensity: 700 cd

Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 387358

Packaging dimensions and weight

- EAN/UPC – product: 8718696778265
- Net weight: 0.45 kg
- Gross weight: 0.58 kg
- Height: 6.5 cm
- Length: 10 cm
- Width: 21.2 cm
- Material number (12NC):
929001215269



Issue date: 2024-09-18
Version: 0.326

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com