

PHILIPS

Filament Bulb Clear
60W A60 B22 x3

LED

2700K

806 lm

15000 h



8718699718237



Experience warm white LED light

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

High-quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Better for your wallet and your planet

Light beyond illumination

- Vintage style, modern LED technology

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Energy savings of up to 90%

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

Vintage-style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: B22
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Lamp dimensions

- Height: 10.4 cm
- Width: 6 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- Efficacy: 115 lm/W

Packaging information

- EAN: 8718699718237
- EOC: 871869971823700
- Product title: LED classic 60W A60 B22 WW CL ND 3CT/4

Power consumption

- Power factor: 0.51
- Voltage: 220-240 V
- Wattage: 7 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): E

Product dimensions and weight

- Length: 10.4 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 1825157

8718699718237

Packaging dimensions and weight
[LEDclassic 60W A60 B22 WW CL ND
3CT/4 UK]

- EAN/UPC - product: 8718699718237
- Net weight: 0.1 kg
- Gross weight: 0.16 kg
- Height: 12 cm
- Length: 7.6 cm
- Width: 21.7 cm
- Material number (12NC):
929001387497

Packaging dimensions and weight
[LED classic 60W A60 B22 WW CL ND
3CT/4]

- EAN/UPC - product: 8718699718237
- Net weight: 0.1 kg
- Gross weight: 0.16 kg
- Height: 12 cm
- Length: 7.6 cm
- Width: 21.7 cm
- Material number (12NC):
929001387491



Issue date: 2024-07-25
Version: 0.178

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com