

PHILIPS

Doris Ceiling Light 17
W

Ceiling Lights

4000K

Nickel

Water Resistant



8718699758943



Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes.

Easy to experience

- Easy installation

Safety

- Moisture resistance

Premium quality

- EyeComfort – light that's easy on the eyes
- Easy to clean

Durability

- Long life span up to 15,000 hours

Highlights

Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

Moisture resistance

Moisture resistance means you can confidently use this product in bathrooms, kitchens, balconies and other spaces where moisture may be a consideration.

EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and

colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Easy to clean

Smooth and easy-to-clean materials mean your home always looks attractive from floor to ceiling.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Colour: Nickel
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bathroom, Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: Water Resistant

Other characteristics

- Lamp current: 142 mA
- Efficacy: 100 lm/W

Product dimensions and weight

- Net weight: 0.57 kg
- Height: 9 cm
- Length: 31.3 cm
- Width: 31.3 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 15,000 h
- Diameter: 313 mm
- Total lumen output fixture: 1700
- Light colour: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- IP code: IP44
- Class of protection: Class I

8718699758943

Packaging dimensions and weight

- EAN/UPC - product: 8718699758943
- Net weight: 0.55 kg
- Gross weight: 0.82 kg
- Height: 10 cm
- Length: 35 cm
- Width: 35 cm



Issue date: 2024-11-21
Version: 0.252

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com