

PHILIPS

Filament Bulb
Smoky 11W T32 E27

LED

1800 K

100 lm

15000 h



8718699759674



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted, traditional bulbs.

High-quality light

- Designed for the comfort of your eyes

Light beyond illumination

- Vintage style, modern LED technology

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Vintage-style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E27
- Dimmable: No
- Lamp Finish: smoky
- Bulb material: Glass

Lamp dimensions

- Height: 14 cm
- Width: 3.2 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h
- Ambient temperature range: -20 to +40 °C

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 1800 K
- Nominal luminous flux: 100 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 818 | CCT of 1800K
- Correlated Colour Temperature (Nom): 1800 K
- Luminous Flux: 100 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 43 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Decorative

Other characteristics

- Efficacy: 43 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699759674
- EOC: 871869975967400
- Product title: LED classic 11W T32 E27 smoky ND RFSRT4

Power

- Power Factor (Fraction): 0.54

Power consumption

- Power factor: 0.54
- Voltage: 220–240 V
- Wattage: 2.3 W
- Wattage equivalent: 11 W
- Power Consumption: 2.3 W

Product dimensions and weight

- Length: 14 cm

Rated values

- Rated lifetime: 15,000 h

Technical specifications

- Frequency: 50–60 Hz
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60 Hz
- Dimmable: No
- Cap base: E27

Packaging dimensions and weight

- EAN/UPC – product: 8718699759674
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 18.5 cm
- Length: 4.5 cm
- Width: 4.5 cm



Issue date: 2025-03-06
Version: 0.341

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com