

PHILIPS

Filament Bulb Frosted
150W A67 E27

LED

2700K

2452 lm

15000 h



8718699764579



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High-quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Light beyond illumination

- Vintage style, modern LED technology

Highlights

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Vintage-style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Dimmable: No
- Lamp Finish: Frosted
- Bulb material: Glass

Lamp dimensions

- Height: 12.1 cm
- Width: 7 cm

Durability

- Number of switch cycles: 20,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 2452 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 827 | CCT of 2700K
- Correlated Colour Temperature (Nom): 2700 K
- Luminous Flux: 2,452 lm
- Stroboscopic effect: 0.4
- Luminous efficacy (rated) (nom.): 140.00 lm/W

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- Efficacy: 140 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699764579
- EOC: 871869976457900
- Product title: LED classic 150W A67 E27 WW FR NDRFSRT4

Power

- Power Factor (Fraction): 0.51

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage: 17.5 W
- Wattage equivalent: 150 W
- Power Consumption: 17.5 W
- Energy efficiency label (EEL): D

Product dimensions and weight

- Length: 12.1 cm

Rated values

- Rated lifetime: 15,000 h

Technical specifications

- Frequency: 50–60 Hz
- EPREL Registration Number: 374905
- Flux measurement reference: Sphere
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60 Hz
- Dimmable: No
- Cap base: E27

Packaging dimensions and weight

- EAN/UPC - product: 8718699764579
- Net weight: 0.03 kg
- Gross weight: 0.06 kg
- Height: 17.7 cm
- Length: 7.5 cm
- Width: 7.5 cm



Issue date: 2025-03-09
Version: 0.330

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com