

PHILIPS

Spot 80W PAR16
GU10

LED

2200-2700K

575 lm

25000 h

Dimming



8718699774097



The right light makes the moment

The Philips LED WarmGlow lamps offer a new experience for dimmable LEDs, by enabling light levels to dim to the warm tones of traditional lamps. You can change the ambience from functional lighting to an inviting and cosy atmosphere.

High-quality light

- True incandescent-like warm white light

Light beyond illumination

- Dimmable

Highlights

Incandescent-like warm white

This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. Ideal for home lighting design

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be

certain that your particular dimmer can be used with this bulb.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: Only with specific dimmers
- Bulb material: Glass

Lamp dimensions

- Height: 5.6 cm
- Width: 5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 25,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 90
- Colour temperature: 2200-2700 K
- Nominal luminous flux: 575 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable, WarmGlow

Other characteristics

- Efficacy: 92 lm/W

Packaging information

- EAN: 8718699774097
- EOC: 871869977409700
- Product title: LED CLA 80W GU10 CRI90 WW 36D WGD SRT4

Power consumption

- Power factor: 0.88
- Voltage: 220-240 V
- Wattage: 6.2 W
- Wattage equivalent: 80 W
- Energy efficiency label (EEL): F

Product dimensions and weight

- Length: 5.6 cm

Rated values

- Rated peak intensity: 950 cd

Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 387456

Packaging dimensions and weight

- EAN/UPC - product: 8718699774097
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm
- Material number (12NC): 929002065903



Issue date: 2024-09-17
Version: 0.181

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com