

# PHILIPS

Reflector 40W R50  
E14 x2

LED

2700K

210 lm

15000 h



8718699774257



## Durable LED accent lighting with a focused bright beam

This directional LED lamp provides a focused beam of warm, white light and is an excellent replacement for traditional reflector lamps.

### High-quality light

- True incandescent-like warm white light

# Highlights

## Incandescent-like warm white



This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E14
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

## Lamp dimensions

- Height: 8.4 cm
- Width: 5 cm

## Design and finishing

- Material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 210 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Other characteristics

- Efficacy: 75 lm/W

## Packaging information

- EAN: 8718699774257
- EOC: 871869977425700
- Product title: LED CLA 40W R50 E14 WW 36D ND RF 2SRT6

## Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 2.8 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): F

## Product dimensions and weight

- Length: 8.4 cm

## Rated values

- Rated peak intensity: 400 cd

#### Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 397588

#### Packaging dimensions and weight

- EAN/UPC - product: 8718699774257
- Net weight: 0.11 kg
- Gross weight: 0.14 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 13 cm
- Material number (12NC):  
929001891118



Issue date: 2024-07-26  
Version: 0.84

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)