

# PHILIPS

Spot 50W PAR16  
GU10

LED

4000K

350 lm

15000 h

Dimming



8718699787745



## Light that shows your home's true colours.

See your home's true colours with Philips CRI90 LED lamps and flood your rooms with natural light. Lamps with a colour rendering index (CRI) closer to 100 are comparable to natural light, and this allows you to see your home's fittings and furnishings the way you always wanted. Don't settle for lights which misrepresent colours – see your home in its true colours with Philips CRI90.

### High-quality light

- Cool, white light

### Create the right light for your home

- Perfect for accent lighting

### Light beyond illumination

- Dimmable

# Highlights

## Cool, white light



This lamp has a colour temperature of 4000K providing you with an extra cool, fresh and crisp light.

## Perfect for accent lighting



Modern lighting with a familiar wide-angle light output (36 degrees), this LED spot is suitable for both accent lighting and general-purpose lighting. It

can be used in recesses and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: Only with specific dimmers
- Bulb material: Glass

## Lamp dimensions

- Height: 5.4 cm
- Width: 5 cm

## Design and finishing

- Material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 90
- Colour temperature: 4000 K
- Nominal luminous flux: 350 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 940 | CCT of 4000K

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable

## Other characteristics

- Efficacy: 87 lm/W

## Packaging information

- EAN: 8718699787745
- EOC: 871869978774500
- Product title: LED CLA 50W GU10 C90 CW 36D D 1PF/6

## Power consumption

- Power factor: 0.84
- Voltage: 220-240 V
- Wattage: 4 W
- Wattage equivalent: 50 W
- Energy efficiency label (EEL): F

## Product dimensions and weight

- Length: 5.4 cm

#### Rated values

- Rated peak intensity: 700 cd

#### Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 391907

#### Packaging dimensions and weight

- EAN/UPC - product: 8718699787745
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 6 cm
- Length: 5.1 cm
- Width: 5.1 cm
- Material number (12NC):  
929002065866



Issue date: 2024-09-18  
Version: 0.105

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)