

PHILIPS

Candle 40W P45
B22

LED

2700K

470 lm

15000 h



8719514309449



State-of-the-art LED light bulb for the home

Philips LED frosted candles provide a soft, diffuse light effect and an exceptionally long life. With a pure and elegant design, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Create the right light for your home

- Perfect for decorative fixtures
- A simple LED for everyday use

Highlights

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs,

and enjoy a perfect lighting solution for over 15 years.

Perfect for decorative fixtures



Modern lighting in Philips LED candles for use in decorative fixtures, such as in chandeliers, ceiling fans, vanity strips and post lights.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: B22
- Dimmable: No

Lamp dimensions

- Height: 8.5 cm
- Width: 4.5 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 470 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 94 lm/W

Packaging information

- EAN: 8719514309449
- EOC: 871951430944901
- Product title: LED 40W P45 B22 WW FR ND 1SRT4 UK

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage: 5 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): F

Product dimensions and weight

- Length: 8.5 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 453231

Packaging dimensions and weight

- EAN/UPC - product: 8719514309449
- Net weight: 0.03 kg
- Gross weight: 0.04 kg
- Height: 12.7 cm
- Length: 4.6 cm
- Width: 6.3 cm



Issue date: 2024-11-28
Version: 0.307

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com