

PHILIPS

Spot 20W MR16
GU5.3 x2

LED

2700K

230 lm

15000 h



8719514314030



Durable LED accent lighting with a focused beam

Philips LED spots provide a focused bright beam, a long life and significant energy savings

High-quality light

- No visible flicker
- True incandescent-like warm white light

Choose a simple replacement for your old lamps

- Similar shape and size as halogen reflectors

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimised, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Incandescent-like warm white



This bulb has a colour temperature of 2,700 K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2,700 K light is ideal for home lighting design

Replaces halogen spots



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Lamp dimensions

- Height: 4.6 cm
- Width: 5.1 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 230 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

Other characteristics

- Efficacy: 76 lm/W

Packaging information

- EAN: 8719514314030
- EOC: 871951431403000
- Product title: LED 20W MR16 WW 36D ND 2SRT6

Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 3 W
- Wattage equivalent: 20 W
- Energy efficiency label (EEL): G

Product dimensions and weight

- Length: 4.6 cm

8719514314030

Rated values

- Rated peak intensity: 600 cd

Technical specifications

- Frequency: 50-60 Hz
- EPREL registration number: 374889

Packaging dimensions and weight

- EAN/UPC - product: 8719514314030
- Net weight: 0.1 kg
- Gross weight: 0.12 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 8.5 cm
- Material number (12NC):
929001344068



Issue date: 2024-08-29
Version: 0.203

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com