

# PHILIPS

## LEDtube EM T8

LED

1500 mm

4000K

G13



8719514445215



# Durable LED task lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. This Philips LED tube is perfect for places that require a lot of light.

### Choose for a sustainable solution

- Enjoy the energy saving of LEDs without sacrificing light quality. Instantly save over 50% in energy by replacing your existing fluorescent tubes (banned by EU regulation since 2023).

### High-quality LED light that lasts for decades

- With a lifetime of 15,000 hours, you can reduce the hassle of frequently replacing your light sources and enjoy a perfect lighting solution for over 15 years.

### Choose a simple replacement for your old fluorescents

- The perfect replacement for linear fluorescent tubes that fits straight into existing luminaires. Simply plug and play without any hassle for rewiring.

# Highlights

**Saves over 50% energy compared to fluorescents**

**Long-lasting for 15,000 hours  
Fast and easy to install**

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: T8
- Socket: G13
- Type of glass: Frosted
- Lamp Finish: Frosted
- Dimmable: No
- Bulb Material: Glass

## Lamp dimensions

- Height: 151.3 cm
- Width: 2.8 cm

## Design and finishing

- Material: Glass

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 h

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 240 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 2000 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

## Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort

## Other characteristics

- Efficacy: 102 lm/W

## Packaging information

- EAN: 8719514445215
- EOC: 871951444521500
- Product title: LED T8 1500mm 20W G13 CW ND 1CT/4 UK

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 19.5 W
- Energy efficiency label (EEL): F

## Product dimensions and weight

- Length: 151.3 cm

## Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 491860
- Ballast Compatibility: EM

## Packaging dimensions and weight

- EAN/UPC - product: 8719514445215
- Net weight: 0.27 kg
- Gross weight: 0.34 kg
- Height: 157.7 cm
- Length: 3.1 cm
- Width: 3.1 cm



Issue date: 2025-01-14  
Version: 0.181

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)