

PHILIPS

Garnet Ceiling Light
40 W

Ceiling Lights

2700K

Black



8720169195271



One fixture. Your switch. Three light settings.

Changing the ambience in your room has never been easier. The Philips' SceneSwitch LED ceiling light lets you set the mood with three unique settings. The combination of main and indirect light give you options that are perfect for your get-together, concentrate and cosy moments. No dimmer or installation required – all you need is your existing switch

Easy to experience

- Easy installation

Light effect

- Indirect light
- Triple-zone light
- Soft harmonious light

Premium quality

- EyeComfort – light that's easy on the eyes

Highlights

Easy installation

No more hassle with installation. Just fix or hang securely on the wall or ceiling, and plug it in. Your new light fitting is now ready to light up your room!

Indirect light

The Volcano lamp shade decorates your space and softly reflects light.

Triple-zone light

The triple-zone light source gives you the flexibility to create the ambience you want.

Soft harmonious light

The right combination of indirect and direct light diffuses a warm glow throughout your space with no glare.

EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Colour: Black
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 20,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 200 mA
- Efficacy: 105 lm/W

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 1.23 kg
- Height: 9.9 cm
- Length: 50 cm
- Width: 50 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 20,000 h
- Diameter: 500 mm
- Total lumen output fixture: 4200
- Light colour: 2700
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- Wattage bulb included: 40
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8720169195271
- Net weight: 1.3 kg
- Gross weight: 3.16 kg
- Height: 54 cm
- Length: 13 cm
- Width: 54 cm
- Material number (12NC):
929003316201



Issue date: 2024-06-17
Version: 0.399

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com