

PHILIPS

Filament Bulb Clear
60W G95 E27

Ultra Efficient

4000K

840 lm

50000 h



8720169202726



Bright LED lighting with excellent light quality

A Philips LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs straight away and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High-quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Better for your wallet and your planet
- Long life bulb - Lasts up to 50 years

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Energy savings of up to 90%

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 50 years.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Type of glass: Clear
- Lamp Finish: Clear
- Dimmable: No
- Bulb material: Glass

Lamp dimensions

- Height: 14 cm
- Width: 9.5 cm

Design and finishing

- Material: Glass

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 840 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

Miscellaneous

- EyeComfort: Yes
- LED innovations: UltraEfficient, EyeComfort

Other characteristics

- Efficacy: 210 lm/W

Packaging information

- EAN: 8720169202726
- EOC: 872016920272600
- Product title: LED CLA 60W G95 E27 4000K CL UE SRT4

Power consumption

- Power factor: 0.4
- Voltage: AC 220-240 V
- Wattage: 4 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): A

Product dimensions and weight

- Length: 14 cm

Technical specifications

- Frequency: 50-60 Hz
- EPREL Registration Number: 1442641

Packaging dimensions and weight

- EAN/UPC - product: 8720169202726
- Net weight: 0.06 kg
- Gross weight: 0.11 kg
- Height: 18.2 cm
- Length: 13.1 cm
- Width: 10.3 cm



Issue date: 2024-11-21
Version: 0.430

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com