

# PHILIPS

## Amigo Fan Ceiling Light 42+20 W

Fan Ceiling Lights

3000/4400/6500 K

White

Dimmable; Remote Control



8720169248786



## Set your desired ambience at your fingertips

Combine customisable light with a comfortable breeze with the Philips LED ceiling fan light, which includes a remote control.

### Easy to experience

- Get year-round use
- Enjoy a comfortable breeze

# Highlights

## Get year-round use

With operation modes for both summer and winter, you'll get the best settings to circulate the air in your space all year round.

## Enjoy a comfortable breeze

Bring an island breeze to any room of your house with the Natural Breeze function, which offers dynamic speed settings for the fan.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Remote control

## Other characteristics

- Lamp current: 330 mA
- Efficacy: 95 lm/W

## Power consumption

- Power factor: 0.9

## Product dimensions and weight

- Net weight: 1.5 kg
- Height: 13.7 cm
- Length: 48.5 cm
- Width: 48.5 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 15,000 h
- Diameter: 485 mm
- Total lumen output fixture: 4400
- Light colour: 3000/4400/6500
- Mains power: AC 220-240
- Fixture dimmable: Yes
- LED: Yes
- IP code: IP20
- Class of protection: Class II

8720169248786

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169248786
- Net weight: 1.5 kg
- Gross weight: 2.32 kg
- Height: 51.5 cm
- Length: 15.5 cm
- Width: 51 cm



Issue date: 2024-11-21  
Version: 0.304

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)