

PHILIPS

UltraEfficient Spot
50 W PAR16 GU10

Ultra Efficient

4000K

375 lm

50000 h

Dimming



8720169307902



Ultra-efficient spot, sustainable lamp with dimmable function

Philips LED spots provide a focused bright beam, an exceptionally long life, and saving up to 47% energy. This spot is the perfect long-lasting replacement for 50 W spots with a GU5.3 cap.

Choose a simple replacement for your old lamps

- Similar shape and size to standard halogen bulb

Choose for a sustainable solution

- Long life bulb - Lasts up to 50 years

High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Replaces standard halogen



With its beautifully shaped design and familiar dimensions, this is a modern lighting energy-saving, standard, LED bulb. The perfect sustainable

replacement for traditional standard halogen bulbs.

Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 50 years.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: Only with specific dimmers
- Bulb material: Glass

Lamp dimensions

- Height: 5.4 cm
- Width: 5 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 375 lm

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort, UltraEfficient

Other characteristics

- Efficacy: 178 lm/W

Packaging information

- EAN: 8720169307902
- EOC: 872016930790200
- Product title: LEDClassic 50W GU10 CW 36D DIM UE SRT4

Power consumption

- Power factor: 0.7
- Voltage: AC 220-240 V
- Wattage: 2.1 W
- Wattage equivalent: 50 W

Product dimensions and weight

- Length: 5.4 cm

Rated values

- Rated peak intensity: 650 cd

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8720169307902
- Net weight: 0.22 kg
- Gross weight: 0.29 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2024-12-31
Version: 0.98

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com