

PHILIPS

UltraEfficient Spot
50 W PAR16 GU10

Ultra Efficient

4000K

375 lm

50000 h

Dimming



8720169307902



Ultra-efficient spot, sustainable lamp with dimmable function

Philips LED spots provide a focused bright beam, an exceptionally long life, and saving up to 47% energy. This spot is the perfect long-lasting replacement for 50 W spots with a GU5.3 cap.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Lamp Finish: Clear
- Dimmable: Only with specific dimmers
- Bulb material: Glass

Lamp dimensions

- Height: 5.4 cm
- Width: 5 cm

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 50,000 h

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 36 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Nominal luminous flux: 375 lm

Miscellaneous

- EyeComfort: Yes
- LED innovations: EyeComfort, UltraEfficient

Other characteristics

- Efficacy: 178 lm/W

Packaging information

- EAN: 8720169307902
- EOC: 872016930790200
- Product title: LEDClassic 50W GU10 CW 36D DIM UE SRT4

Power consumption

- Power factor: 0.7
- Voltage: AC 220-240 V
- Wattage: 2.1 W
- Wattage equivalent: 50 W

Product dimensions and weight

- Length: 5.4 cm

Rated values

- Rated peak intensity: 650 cd

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8720169307902
- Net weight: 0.22 kg
- Gross weight: 0.29 kg
- Height: 12.7 cm
- Length: 5.3 cm
- Width: 6.3 cm



Issue date: 2025-03-09
Version: 0.106

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com