

# PHILIPS

Panel Ceiling SQ  
15 W 2700K white

Ceiling Lights

2700K

White

Dimmable

8720169347939



## One fixture. Your switch. Three light settings.

Sometimes you feel like a change in ambiance to suit whatever you're doing. With this Philips SceneSwitch LED panel, you can easily change the light setting with your existing switch. No dimmer or additional installation required.

### Match your interior

- Super slim design

### Light effect

- Uniform light distribution

### Premium quality

- EyeComfort – light that's easy on the eyes
- Easy to clean

# Highlights

## Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

## Uniform light distribution

Throw light across your rooms in an even and uniform manner.

## EyeComfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, colour rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output and colour for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Easy to clean

Smooth and easy-to-clean materials mean your home always looks attractive from floor to ceiling.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Colour: White
- Material: Plastic

## Durability

- Average life (at 2.7 hrs/day): 20 year(s)
- Number of switch cycles: 20,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 80
- Warm-up time to 60% light: <2

**Miscellaneous**

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- LED innovations: EyeComfort
- Extra Features: Dimmable

**Other characteristics**

- Lamp current: 90 mA
- Efficacy: 126 lm/W

**Power consumption**

- Power factor: 0.9

**Product dimensions and weight**

- Net weight: 1.8 kg
- Height: 4 cm
- Length: 40 cm
- Width: 40 cm

**Service**

- Warranty: 5 year(s)

**Technical specifications**

- Lifetime up to: 20,000 h
- Total lumen output fixture: 1900
- Light colour: 2700
- Mains power: AC 220-240
- Fixture dimmable: Step Dim – Do not use with dimmer
- LED: Yes
- IP code: IP20
- Class of protection: Class II

**Packaging dimensions and weight**

- EAN/UPC - product: 8720169347939
- Net weight: 1.9 kg
- Gross weight: 2.57 kg
- Height: 45.2 cm
- Length: 44.9 cm
- Width: 5.9 cm



Issue date: 2025-02-14  
Version: 0.195

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)