

# PHILIPS

## Ceiling Light 36W

Ceiling Lights

4000/6500/2700K

Silver

SceneSwitch



6922341906664



## One fixture. Your switch. Three light settings.

Create the right ambience every time. With just a couple of clicks on the remote control, Philips LED all-in-one ceiling light gives you the flexibility and convenience to choose between a range of light settings for every moment.

### Easy to experience

- Easy installation

### Light effect

- Cozy light effect

### Premium quality

- EyeComfort - light that's easy on the eyes
- Easy to clean

### Control

- Tunable - from warm white to cool daylight
- Tunable with wall switch

# Highlights

## Easy installation

No more hassle in installation. Just fix or hang securely on the wall or ceiling, and plug in, now this luminaire is ready to light on.

## Cozy light effect

Create a warm, comforting environment to wind down and relax in.

## Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## Easy to clean

Smooth and easy-to-clean materials mean your home always looks attractive from floor to ceiling.

## Tunable - from warm white to cool daylight

Tunable lighting lets you change the color of light to match your mood or activity. Warm white is ideal for relaxation, cool daylight for invigorating focus.

## Tunable with wall switch

An easy-to-use wall switch allows you to shift between different light colors.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: Silver
- Material: Metal, Plastic

## Durability

- Number of switch cycles: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

**Light characteristics**

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

**Miscellaneous**

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Garage
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: Yes
- Extra Features: SceneSwitch

**Other characteristics**

- Lamp current: 185 mA
- Efficacy: 72 lm/W

**Product dimensions and weight**

- Net weight: 1.35 kg
- Height: 8.7 cm
- Length: 46 cm
- Width: 46 cm

**Service**

- Warranty: 1 year(s)

**Technical specifications**

- Lifetime up to: 15,000 hour(s)
- Diameter: 460 mm
- Total lumen output fixture: 2600
- Light color: 4000/6500/2700
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- IP code: IP20
- Class of protection: Class I

**Packaging dimensions and weight**

- EAN/UPC - product: 6922341906664
- Net weight: 0.86 kg
- Gross weight: 1.9 kg
- Height: 52.5 cm
- Length: 12.5 cm
- Width: 54.5 cm
- Material number (12NC): 929002504409



Issue date: 2024-11-18  
Version: 0.218

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)