

PHILIPS


CL950 Ceiling Light
55W

Smart LED

Tunable white

IP40/Plastic/White

6941970613385



Smart lighting for you daily living

Light up your space with Philips EyeComfort LED ceiling light that provides a comfortable light source and ease to your eyes.

Smart control

- Voice control with Google Assistant, Alexa or Siri Shortcuts

Light modes

- Customize Scenes with preset dynamic light modes.
- Trigger different light modes

Highlights

Voice Control

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change color, and set custom light Scenes.

Customized Scenes

Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, WiZmote or voice.

Trigger different light modes

" By setting Rhythms for the room in the WiZ app, you can make your sensor trigger different light modes at different times of the day"

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

Extra feature/accessory incl.

- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 97
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom
- EyeComfort: Yes

Other characteristics

- Lamp current: 280 mA
- Efficacy: 80 lm/W

Power consumption

- Power factor: 0.9
- Voltage: 220-240 V

Product dimensions and weight

- Net weight: 3.1 kg
- Height: 7.3 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 500 mm
- Total lumen output fixture: 4400
- Light color: 2700-6500
- Fixture dimmable: Wireless Dim - Do not use with dimmer
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 55
- IP code: IP40
- Class of protection: Class II

Packaging dimensions and weight

- Net weight: 2.7 kg
- Gross weight: 3.4 kg
- Height: 0
- Length: 0
- Width: 0
- Material number (12NC): 929004110909



Issue date: 2024-08-09
Version: 0.50

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com