

PHILIPS

Downlight

Recessed Lights

4000K

White

White

8718696170892



Comfortable LED light that's easy on your eyes

Light up your space with Philips EyeComfort LED Downlight that provides a comfortable light source and ease to your eyes.

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Durability

- Long life span up to 15,000 hours

High quality LED light that lasts for decades

- Reduced glare. Increased comfort.

Highlights

Suitable for low ceilings Slim design Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

EyeComfort with Interlaced optics

Interlaced optics technology enhances the overall lighting experience in your every-day life. Imprinted with 3D patterns to help diffuse light, the micro-lens technology produce an

even distribution of light which reduces glare significantly. This illumination is not only a soft and uniform light which brings more comfort to your eyes, but it also cleverly redistributes light for less glaring illumination in the lit area.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 7,500

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 46 mA
- Efficacy: 69 lm/W

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.036 kg
- Cut out length: 8.0 cm
- Cut out width: 8.0 cm
- Height: 3.5 cm
- Length: 9 cm
- Recessed distance: 8.7 cm
- Width: 9 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 90 mm
- Total lumen output fixture: 380
- Light color: 4000
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: No
- Wattage bulb included: 5.5
- IP code: IP20
- Class of protection: Class II

**Packaging dimensions and weight
[59444 MESON 080 6W 40K WH
recessed LED]**

- EAN/UPC - product: 8718696170892
- Net weight: 0.05 kg
- Gross weight: 0.09 kg
- Height: 9.7 cm
- Length: 5.4 cm
- Width: 9.6 cm

**Packaging dimensions and weight
[59444 Meson 080 5.5W 40K
recessed IO]**

- EAN/UPC - product: 8718696170892
- Net weight: 0.04 kg
- Gross weight: 0.05 kg
- Height: 9.2 cm
- Length: 4.1 cm
- Width: 9.2 cm



Issue date: 2024-11-21
Version: 0.204

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com