

PHILIPS

Amigo Fan Ceiling Light 42+20W

Fan Ceiling Lights

3000/4400/6500K

White

Dimmable; Remote Control



8720169248786



Set your desired ambiance at your fingertips

Combine customizable light with a comfortable breeze with the Philips LED ceiling fan light, which includes a remote control.

Easy to experience

- Get year-round use
- Enjoy a comfortable breeze

Highlights

Get year-round use

With operation modes for both summer and winter, you'll get the best settings to circulate the air in your space all year round.

Enjoy a comfortable breeze

Bring an island breeze to any room of your house with the Natural Breeze function, which offers dynamic speed settings for the fan.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: Plastic

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes

Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Fan Ceiling Lights
- EyeComfort: Yes
- Extra Features: Dimmable, Remote Control

Other characteristics

- Lamp current: 330 mA
- Efficacy: 95 lm/W

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 1.5 kg
- Height: 13.7 cm
- Length: 48.5 cm
- Width: 48.5 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 485 mm
- Total lumen output fixture: 4400
- Light color: 3000/4400/6500
- Mains power: AC 220-240
- Fixture dimmable: Yes
- LED: Yes
- Wattage bulb included: 42+20
- IP code: IP20
- Class of protection: Class II

8720169248786

Packaging dimensions and weight

- EAN/UPC - product: 8720169248786
- Net weight: 1.5 kg
- Gross weight: 2.32 kg
- Height: 51.5 cm
- Length: 15.5 cm
- Width: 51 cm
- Material number (12NC): 929003338201



Issue date: 2024-06-24
Version: 0.292

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com