

PHILIPS

Circular fluorescent

TL-E Standard colours

40 W

G10q

Cool daylight

928027405436



Reliable, functional lighting

Philips TL/TLDs produce light efficiently, resulting in fewer replacements. They provide functional lighting that gives sufficient light levels for common areas.

Gives you bright light

- Standard colors with moderate color rendering
- High initial light output

Highlights

Standard colors High initial light output

High Light output provides better light quality with more brightness and allows more vibrance in home application.

Specifications

Bulb characteristics

- Socket: G10q
- Dimmable: No

Durability

- Nominal lifetime: 8,000 hour(s)

Light characteristics

- Color rendering index (CRI): 72
- Light Color Category: Cool Daylight
- Correlated Color Temperature (Nom): 6200
- Luminous Flux: 2,500 lm
- Luminous Efficacy (rated) (Nom): 62 lm/W

Power consumption

- Wattage: 40 W
- Power Consumption: 40.0 W

Technical specifications

- Light output: 2,470 lm
- Shape: Circular fluorescent
- Dimmable: Yes
- Cap-Base: G10q

Packaging dimensions and weight

- EAN/UPC - product: 8711500559913
- Net weight: 0.25 kg
- Gross weight: 0.39 kg
- Height: 41 cm
- Length: 3.5 cm
- Width: 41 cm



Issue date: 2024-11-21
Version: 0.443

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com