

PHILIPS

Linear fluorescent
tube

TL-D Standard colours

58 W

G13

Cool daylight

928049005482



Reliable, functional lighting

Philips Color 80s offer higher light output for extra brightness and better ambiance. They are suitable for applications where light quality is important for a more vibrant experience.

Gives you bright light

- Standard colors with moderate color rendering
- High initial light output

Highlights

Standard colors High initial light output

High Light output provides better light quality with more brightness and

allows more vibrance in home application.

Specifications

Bulb characteristics

- Socket: GU10
- Dimmable: No

Durability

- Nominal lifetime: 13,000 hour(s)

Light characteristics

- Color rendering index (CRI): 72
- Light Color Category: Cool Daylight
- Correlated Color Temperature (Nom): 6200
- Luminous Flux: 4,000 lm

Power consumption

- Wattage: 58 W
- Power Consumption: 58.5 W

Technical specifications

- Light output: 3,925 lm
- Shape: Linear fluorescent tube
- Dimmable: Yes
- Cap-Base: G13 | Medium Bi-Pin Fluorescent

Packaging dimensions and weight

- EAN/UPC - product: 8711500702753
- Net weight: 0.23 kg
- Gross weight: 0.26 kg
- Height: 2.7 cm
- Length: 150 cm
- Width: 2.7 cm
- Material number (12NC): 928049005482



Issue date: 2024-06-19
Version: 0.555

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com