

# PHILIPS

Desk Lamp

myHomeOffice

66150 seerbase

portable light

white

929003548601



## Advanced desk lighting for a brighter future

RGB battery indicator. 15min auto-off mode.

### Easy to experience

- Rechargeable battery

### Control

- Convenient brightness control Linear dimming function (remote control not included)

# Highlights

## Rechargeable battery

Works without plug-in charger.

## Convenient brightness control Linear dimming function (remote control not included)

Lets you smoothly shift between different brightness levels to find the perfect mood.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Plastic

## Extra feature/accessory incl.

- Batteries included: Yes

## Light characteristics

- Color rendering index (CRI): 90

## Miscellaneous

- Especially designed for: Home office & Study
- EyeComfort: Yes

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- LED: Yes
- IP code: IP20

## Packaging dimensions and weight

- EAN/UPC - product: 8719514495814
- Net weight: 0.33 kg
- Gross weight: 0.51 kg
- Height: 213 mm
- Length: 163 mm
- Width: 143 mm
- Material number (12NC): 929003548601



Issue date: 2024-06-24  
Version: 0.64

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)