

# PHILIPS

## Light Strip 5m

Light Strips

3000K

Transparent



31058/31/66



## Bring imagination to light

Flexible LED strips can be curved around corners, trimmed and connected to any required length. Take your creativity off the straight and narrow, and experiment in exploring new ways to use the LED strip!

### **Ease of use**

- Smooth surface finish for easy cleaning

### **Long lifespan**

- Extremely long life 20,000 hours

### **Energy saving**

- Built-in LED, as part of the system

# Highlights

## Easy to maintain



## Extremely long life



A light source you can trust. Philips LED lights offer an extremely long-life of at least 20,000 hours (which equals 20 years on basis of an average use of 3 hours / day with an amount of at least of 13,000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

## Integrated LED light source



A light source you can trust. With integrated LED light source, you won't have to worry about maintenance or lamp replacement while having the perfect light ambiance in your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: Transparent
- Material: Plastic

## Durability

- Number of switch cycles: 10,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

**Extra feature/accessory incl.**

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: No
- Power adapter included: No
- Remote control included: No

**Light characteristics**

- Color consistency: 5 SDCM
- Color rendering index (CRI): 80

**String light/Lightstrip**

- Extendibility: No

**Miscellaneous**

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Hallway
- Style: Contemporary
- Type: Light Strips
- EyeComfort: No

**Other characteristics**

- Lamp current: 40 mA
- Efficacy: 81 lm/W

**Product dimensions and weight**

- Net weight: 0.109 kg
- Height: 0.2 cm
- Length: 500 cm
- Width: 0.8 cm

**Service**

- Warranty: 1 year(s)

**Technical specifications**

- Lifetime up to: 20,000 hour(s)
- Total lumen output fixture: 325
- Light color: 3000
- Mains power: DC 12
- Fixture dimmable: No
- LED: Yes
- Wattage bulb included: 4(16)
- Maximum wattage replacement bulb: 18 W
- IP code: IP20
- Class of protection: Class III
- Number of light sources: 1



Issue date: 2024-06-17  
Version: 0.591

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)