

PHILIPS

Pomeron Recessed
Light


Recessed Lights

2700K

White



59776/31/H0



Essential lighting for a bright home

Manipulate the direction of your light in different ways with Philips Pomeron LED spotlight's adjustable head in 2 axis rotation. With a stylish white design that enhances your décor, bask in strong, focused beam with an accented feel.

Easy to Experience

- Adjustable light angle

Energy saving

- Built-in Philips conventional ballast

Highlights

Adjustable light angle

Energy efficient, long lasting

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 7,500

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Yes
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 30 degree(s)
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 62 mA
- Efficacy: 55 lm/W

Product dimensions and weight

- Net weight: 0.18 kg
- Cut out length: 7.0 cm
- Cut out width: 7.0 cm
- Height: 6.2 cm
- Length: 9 cm
- Recessed distance: 3.15 cm
- Width: 9 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 107.4 mm
- Total lumen output fixture: 390
- Light color: 2700
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- Wattage bulb included: 7
- Maximum wattage replacement bulb: 7 W
- IP code: IP20
- Class of protection: Class II
- Number of light sources: 1

Packaging dimensions and weight

- EAN/UPC - product: 6947830434565
- Net weight: 0.12 kg
- Gross weight: 0.16 kg
- Height: 88 mm
- Length: 94 mm
- Width: 94 mm
- Material number (12NC): 915005444701



Issue date: 2024-06-17
Version: 0.227

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com