

# PHILIPS

LEDtube EM T8

LED

600mm

6500K

G13

Non-dimmable

8718696525074



## Durable LED task lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. This Philips LED tube is perfect for the places that need a lot of light.

### Choose for a sustainable solution

- Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 50% in energy by replacing your existing fluorescent tubes (banned by EU regulation since 2023).

### High quality LED light that lasts for decades

- With a lifetime of 15,000 hours, you can reduce the hassle of frequently replacing your light sources and enjoy a perfect lighting solution for over 15 years.

### Choose a simple replacement for your old fluorescents

- The perfect replacement for linear fluorescent tubes that fits straight into existing luminaires. Simply plug and play without any hassle for rewiring.

# Highlights

**Saves over 50% energy compared to fluorescents**

**Long lasting for 15,000 hours**  
**Fast and easy to install**

# Specifications

## Bulb characteristics

- Shape: Tube
- Lamp shape: T8
- Socket: G13
- Type of glass: Frosted
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Glass

## Bulb dimensions

- Height: 60.25 cm
- Width: 2.78 cm

## Design and finishing

- Material: Glass

## Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 °C to 45 °C
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Color rendering index (CRI): 73
- Color temperature: 6500 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: 0.5 s
- Correlated Color Temperature (Nom): 6500 K
- Luminous Flux: 800 lm
- Luminous Efficacy (rated) (Nom): 100.00 lm/W

## Miscellaneous

- EyeComfort: Yes
- Approval Marks: RoHS compliance, KEMA Keur certificate
- LED Innovations: EyeComfort

## Other characteristics

- Efficacy: 100 lm/W
- EU RoHS compliant: Yes

## Packaging information

- Product family: EyeComfort

## Power

- Power Factor (Fraction): 0.5

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 8 W
- Wattage equivalent: 18 W
- Power Consumption: 8 W

## Product dimensions and weight

- Length: 60.27 cm

## Rated values

- Rated lifetime: 15,000 hour(s)

## Technical specifications

- Frequency: 50-60 Hz
- Line Frequency: 50 to 60 Hz
- Dimmable: No
- Cap-Base: G13 | Medium Bi-Pin Fluorescent
- Ballast Compatibility: EM

## Packaging dimensions and weight

- EAN/UPC - product: 8718696525074
- Net weight: 0.09 kg
- Gross weight: 0.13 kg
- Height: 3 cm
- Length: 64.1 cm
- Width: 3 cm



Issue date: 2024-12-25  
Version: 0.644

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)