

# PHILIPS

LED Strip Extension  
1m

Smart LED

Color & Tunable White

Low Voltage

IP20/Pu-coating

8719514261525



## Colorful light that matches your mood

Extend your Philips smart LED strip up to 10 metres with the flexible, full-color 1-metre extension strip, which lets you bring even more color to your home. This LED strip is WiZ connected. Use with your existing Wi-Fi to control with the WiZ app or your voice.

### Smart control

- Control anywhere with your smartphone.
- Voice control with Google Assistant, Alexa or Siri Shortcuts

### Smart features

- Automate your light with schedules

### Smart devices

- Shape lights your way
- Starter Kit extension -- go further with its flexibility.

### Light modes

- Tunable warm to cool white and preset modes
- Millions of colors and dynamic light modes
- Customize Scenes with preset dynamic light modes.

# Highlights

## Control from anywhere

Control your WiZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WiZ app is available for iOS and Android.

## Voice Control

Get hands-free control of your lights by using your voice and Google Assistant, Amazon Alexa or Siri Shortcuts. Use simple voice commands to turn lights on or off, brighten and dim, change color, and set custom light Scenes.

## Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

## Shape lights your way

Extendable up to 10 meters (extension sold separately). Cut it and tape it on any surface, can go around angles.

## Shape lights your way

Only works with Strip Starter Kit (sold separately). Extendable up to 10 meters, cut it and tape it on any surface, can go around angles.

## Tunable warm to cool white and preset modes

Choose from a wide range of energizing cool white to soft warm white, or simply select from the preset modes such as Focus and Relax to create the best ambience for your activities.

## Millions of colors and dynamic light modes

Choose from a palette of millions of light colors to create an amazing atmosphere in your home. Enjoy the subtle differences that our dynamic light effects glow your environment

## Customized Scenes

Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, WiZmote or voice.

# Specifications

## Design and finishing

- Color: White
- Material: Plastic

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: No
- Power adapter included: No
- Remote control included: No

## Light characteristics

- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Functional
- EyeComfort: Yes

## Power consumption

- Voltage: 12 V

## Product dimensions and weight

- Net weight: 0.05 kg
- Height: 0.22 cm
- Length: 100 cm
- Width: 1.2 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 800
- Light color: 2700-6500 (RGB)
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 11
- IP code: IP20
- Class of protection: Class III

8719514261525

**Packaging dimensions and weight**

- EAN/UPC - product: 8719514261525
- Net weight: 0.05 kg
- Gross weight: 0.08 kg
- Height: 16.2 cm
- Length: 4.7 cm
- Width: 7.7 cm



Issue date: 2024-11-21  
Version: 0.48

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)