

# PHILIPS

Downlight

Functional

DL262

white

8719514331396



## Robust LED downlight which lasts for years

Philips LED Slim Downlight delivers a natural light effect for use in general lighting applications. It is a slim masterpiece for low ceilings, creating an elegant ambiance anywhere at home. Comfortable light that's easy on your eyes.

### Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

### Light effect

- Bright light with uniform distribution

### Safety

- No harmful UV radiation

### Durability

- Long life span up to 15,000 hours

# Highlights

**Suitable for low ceilings Slim design**  
**Bright light with uniform distribution**  
 To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

**No harmful UV radiation**  
 The product is designed to eliminate any potentially harmful UV radiation.

**Long life span up to 15,000 hours**  
 Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor

## Design and finishing

- Color: White
- Material: Plastic

## Durability

- Number of switch cycles: 7,500

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 110 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 50 mA
- Efficacy: 80 lm/W

## Power consumption

- Power factor: 0.51

## Product dimensions and weight

- Net weight: 0.129 kg
- Cut out length: 10.0 cm
- Cut out width: 10.0 cm
- Height: 2 cm
- Recessed distance: 5 cm

## Service

- Warranty: 3 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 120 mm
- Total lumen output fixture: 480
- Light color: 6500
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- IP code: IP20
- Class of protection: Class II

## Packaging dimensions and weight

- EAN/UPC - product: 8719514331396
- Net weight: 0.13 kg
- Gross weight: 0.25 kg
- Height: 16 cm
- Length: 2.5 cm
- Width: 12.5 cm
- Material number (12NC): 929002659801



Issue date: 2024-09-17  
Version: 0.87

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)