

PHILIPS

Bulb 40W P45 E27

LED

6500K

339lm

12000h

8720169278769



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old bulbs

- Similar shape and size as incandescent luster

Light beyond illumination

- Instant on

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on

Replaces luster incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED luster. The perfect sustainable replacement for traditional incandescent lusters.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E27
- Type of glass: Frosted
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Bulb dimensions

- Height: 8.7 cm
- Width: 4.5 cm

Design and finishing

- Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 12,000 hour(s)

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: instant full light
- Color Code: 865 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- Efficacy: 83 lm/W

Packaging information

- EAN: 8720169278769
- EOC: 872016927876900
- Product title: LEDBulb 3W E27 6500K 230V P45 IDOL

Power consumption

- Power factor: 0.41
- Voltage: AC 220-240 V
- Wattage: 3 W
- Wattage equivalent: 25 W

Product dimensions and weight

- Length: 8.7 cm

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8720169278769
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 8.8 cm
- Length: 4.7 cm
- Width: 4.7 cm



Issue date: 2024-11-21
Version: 0.155

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com