

# PHILIPS

Bulb 80W A60 E27

LED

2700/3000/4000/5000/6500  
K

900lm

15000h

Dimming

8720169335943



## Selectable colour temperatures help you to make the right choice

Bring human-centric lighting into your life with this smart WiZ LED A67 whites bulb. Apply different shades of warm to cool white to help you focus or relax. You can set schedule to turn lights on and off according to your daily or weekly routines, control with your smartphone or your voice and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

### High quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

### Light beyond illumination

- Instant on

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Instant on

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Bulb Finish: Frosted
- Dimmable: Only with specific dimmers
- Bulb Material: Plastic

## Bulb dimensions

- Height: 11.5 cm
- Width: 6 cm

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000 hour(s)

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2700/3000/4000/5000/6500 K
- Nominal luminous flux: 900 lm

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

## Other characteristics

- Efficacy: 112 lm/W

#### Packaging information

- EAN: 8720169335943
- EOC: 872016933594300
- Product title: LEDBulb 8W E27 DS FR DIM 1CT/6 ID

#### Power consumption

- Power factor: 0.7
- Voltage: AC 220-240 V
- Wattage: 8 W
- Wattage equivalent: 80 W

#### Product dimensions and weight

- Length: 11.5 cm

#### Technical specifications

- Frequency: 50-60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 8720169335943
- Net weight: 0.04 kg
- Gross weight: 0.06 kg
- Height: 11.9 cm
- Length: 6.3 cm
- Width: 6.3 cm
- Material number (12NC): 929003785287



Issue date: 2024-09-14  
Version: 0.19

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)