

PHILIPS

5m with cord set
24W Warm White

Light Strips

6500K

White

Dual Brightness

8720169351639



Incredibly bright colors from end to end

Full-color RGB light strips in 5m, 10m, and 15m lengths add drama and mood to any location in your home. The included remote control lets you easily and conveniently dim, change colors and scenes, and turn light strips on and off. Dynamic color-changing light effects create a dramatic, cozy, fun, or romantic ambiance. Incredibly bright, uniform light from end to end with no shadows or dark spots.

Easy installation

- Cut to size

Easy and safe to use

- Special coating makes the strip safe to touch

Light modes

- Incredibly bright, uniform white light from end to end

Ultimate flexibility in installation

- Heavy-duty 3M adhesive on a slim strip

Plug and Play

- Plug-and-play: easy installation

Highlights

Cut to size

Easily cut light strips to fit your spaces. Cut marks on the light strip indicate where to cut.

Completely safe to touch

A special coating offers enhanced protection for electrical parts, ensuring safe installation and maintenance, as well as protection against dust and moisture.

Incredibly bright white light

This high-intensity LED strip light beautifies your space with incredibly bright, uniform light. Simply plug and play to create your perfect ambiance.

Plug-and-play: easy installation

Our plug-and-play light strips are simple to install, so you can start enjoying them immediately. Everything you need is included in the box.

Light strip adheres securely anywhere

Adhere the light strip anywhere you want with the high-quality adhesive backing

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- On/off switch on wire: Yes
- Power adapter included: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 3.5 SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

String light/Lightstrip

- Extendibility: No

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office, Hallway
- Style: Contemporary
- Type: Light Strips
- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dual Brightness

Other characteristics

- Lamp current: 185 mA
- Efficacy: 15 lm/W

Power consumption

- Power factor: 0.5

Product dimensions and weight

- Net weight: 0.122 kg
- Height: 0.13 cm
- Length: 1,000 cm
- Width: 0.8 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 370
- Light color: 6500
- Mains power: AC 220-240
- Fixture dimmable: No
- LED: Yes
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8720169351639
- Net weight: 0.12 kg
- Gross weight: 0.27 kg
- Height: 26 cm
- Length: 4.7 cm
- Width: 19.2 cm
- Material number (12NC):
929004145107



Issue date: 2024-09-17
Version: 0.58

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com